


CRUZE

pleated&cellular



FIT *to* FRAME


YOU SHOULD HAVE



Measuring Tape



Notepad




Pencil

FOLLOW THE INSTRUCTIONS AND REMEMBER TO DOUBLE CHECK YOUR MEASUREMENTS AS YOU GO ALONG

STEP 1

Measure the width of the visible glass at the top, middle and bottom area of each window where the glass meets the rubber bead. Order the smallest of the three measurements.



Check the distance between the edge of the beading and any obstructions i.e. window handles. The handle should be at least 35mm from the depth of the window glass.




Minimum & Maximum Sizes

Minimum Width:	200mm
Maximum Width:	1500mm
Minimum Drop:	150mm
Maximum Drop:	2300mm
Maximum Area:	3m ²

Disclaimer: Maximum width of 1500mm only available up to a maximum drop of 2000mm. Maximum drop of 2300mm only available up to a maximum width of 1300mm.

STEP 2

Measure the height of the visible glass at the three points accross the area of each window where the glass meets the rubber bead. Order the smallest of the three measurements.



DO NOT INCLUDE ANY OF THE BEADING OR RUBBER SEALS IN YOUR MEASUREMENT



WARNING

Young children can be strangled by loops in pull cords, chains, tapes and inner cords that operate the product.

To avoid strangulation and entanglement, keep cords out of reach of young children. Cords may become wrapped around a child's neck. Move beds,cots and furniture away from window covering cords.

Do not tie cords together. Make sure cords do not twist and create a loop.

